

HL-05 Recirculating Coolers (Low Temp. Models)

Manufacturer:

SKU#: 8194-10-0708

Powerful recirculating coolers, the HL Models provide a wide range of cooling capacities with temperature reliability. Innovative control system, with a dynamic pumping capacity, and ideal for external temp. applications. Broad range of models to choose from based on working temperature range.



Product Description

Operating features Temperature range is from -20 ~40 . Bright LED water level indicator can be easily identified. Low fluid level and dry-running protection when triggered shows an error symbol on the display and an audible sound. If the equipment operates at 40 or above due to the external environment, user can simply identify the error with a visual or an audible sound. Designed to simplify operation with a touch screen type display. - Easy-to-read VFD display with interactive touch keys. - Setting and resolution indication 0.1 / . - Quick keypad lock prevents accidental parameter changes. - Signal indicator for operation status. Constructional features The refrigerating system is designed to reduce energy consumption and to maximize in refrigerating efficiency. Eco-friendly R-404A / R507 refrigerant is used to prevent environmental pollution. Double service valve is used to prevent refrigerant leakage. Removable gridded vent for reducing condenser contamination and to facilitate cleanliness. A wide (120mm / 4.72) solution inlet is for easy and safe pouring of solution into the recirculating cooler. Pressure gauge comes standard for observing the pump pressure The refrigeration system can be observed easily to diagnostic at a glance by high / low pressure gauges. (HL-25H, 35H, 45H, 55H models) Wheels allow for easy mobility. The beautifully designed and compact. Different types of pumps come standard with the recirculating cooler to provide versatility. Warning alarm/monitoring system. - Over temperature. - Lack of bath solutions. Variety of accessories is available to meet user s different lab environment needs. (Refer to accessories)

HL-05 Recirculating Coolers (Low Temp. Models) Specification


Model	HL -05	HL -10	HL -15	HL -20	HL -15H	HL -20H	HL -25H	HL -35H	HL -45H ²⁾	HL -55H ²⁾
Temperatu Working T -20 to 40 /										
re 1)	emperatu	r -4 to 104								
(bath fluid	(bath fluid e									
:	range									
Ethtylene	(/)									
glycol mix										
1:1 Water)									
Temperat	Temperatu 1 / 1.8									
re stability	1									
at 15 , (/)										
Cooling	at 20 (kw)	0.60	0.07	1.45	1.80	1.45	1.80	2.50	3.30	6.50
capacity										
(bath fluid										
: Ethtylene	9									
glycol mix										
1:1 Water)									
at 10 (kw)	0.50	0.60	1.15	1.50	1.15	1.50	1.80	2.30	4.50	6.00

1

at 0 (kw) at -10 (kw) at -20 (kw) Pump	0.18 0.04	0.42 0.32 0.14 50 / 13.2	0.86 0.62 0.30 40 / 10.57	1.15 0.85 0.40 70 / 18.49	0.86 0.62 0.30	1.15 0.85 0.40	1.10 0.65 0.40	1.70 1.00 0.55	3.00 2.10 1.20	4.10 2.50 1.50
Max. pressure (bar / psi)		3.3 / 47.9	6 / 87.0							
Dimension	Max,. filling capacity (L, cu ft)	7.5 / 0.26	13.5 / 0.47	' 13.5 / 0.47	25 / 0.88	39 / 1.37				
For tubing dia (mm / inch)	20 / 3/4	20 / 3/4								
Overall (WxLxH, mm / inch	405 620 710 /) 15.9 24.4	515 715 835 / 20.3 28.1	515 715 835 / 20.3 28.1	550 900 1140 / 21.7 35.4	605 1045 1300 / 23.8 41.4					
	28.0	32.9	32.9	44.9	51.2					
Net weigh		64.85/	86.5 / 190.7	87.35 / 192.9	91.8 / 202.4	92.65 / 204.3	141.3 / 310.9	146.3 / 321.9	171 10 / 377 22	176 10 / 388 10
(kg / lbs) Electric requirement (230V, 60Hz)		143.0 5.5A	6.5A	7.5A	6.5A	7.5A	9.5A	13.5A	3// 22	300 10
Cat. No.	AAH 65001K	AAH 65011K	AAH 65021K	AAH 65031K	AAH 65121K	AAH 65131K	AAH 65141K	AAH 65151K	-	-
Electric requirement (230V, 50Hz)	q4.5A	5.0A	6.0A	7.0A	6.0A	7.0A	7.5A	12.5A		
Cat. No.	AAH 65002K	AAH 65012K	AAH 65022K	AAH 65032K	AAH 65122K	AAH 65122K	AAH 65142K	AAH 65152K	-	-
Electric requirement (120V, 60Hz)	q10.0A	11.0A	13.0A	15.0A						
Cat. No.	AAH 65003K	AAH 65013K	AAH 65023K	AAH 65033K	-	-	-	-	-	-
Electric red uirement (380V, 60Hz)		03013K	03023K	03033K					5.5A	7.0A
Cat. No.	-	-	-	-	-	-	-	-	AAH	AAH
Electric requirement (380V,	9								65169K 5.0A	65179K 6.0A
50Hz) Cat. No.	-	-	-	-	-	-	-	-	AAH 65168K	AAH 65178K

Your trusted source for Used & New lab equipments, Parts, Factory Clearance instrument service since 1985.







we remove 100% of the risk in buying 'used' laboratory equipment.



as multi-year service agreements are available.

GMI is an industry-leading distributor of brand new laboratory equipment and instruments. We supply a wide range of cutting-edge analytical instruments including centrifuges, gas chromatographs, freezers, thermal cyclers, and more. Choose from more than a thousand of new and innovative lab instruments that meet specifications and come with warranties up to 1 year.

